



47548982

Double SCHUKO soc. out. cover plate, S.1, white glossy

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 2

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 31 mm

Assembling height 22 mm

Cover, door

Cover Full cover plate

Materials

Colour of design line white

Colour white

Colour white

Surface appearance glossy

Metallic colour No

Installation, mounting

For installation in 1gang wall boxes according to DIN 49073-1

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Safety

Protection without enhanced contact protection

