



47548989

Double SCHUKO soc. out. cover plate, S.1, p. white glossy

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 2

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 31 mm

Assembling height 22 mm

Cover, door

Cover Full cover plate

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Metallic colour No

Installation, mounting

For installation in 1gang wall boxes according to DIN 49073-1

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Safety

Protection without enhanced contact protection

