



47633505

SCHUKO soc.out. hinged cover surf.-mtd, enhncd contact prot., W.1, grey matt

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Hollow base ample room for wiring under the bases of the inserts

Main electrical features

Rated voltage 250 V AC

Rated current 16 A

Cover, door

Hinged covers with hinged cover that falls back, manual clip-in

Cover Complete housing

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Terminal with Wago clip-in 2-wire connection terminal for wiring ; with two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection with plug-in terminals

Cable

Wire with one entry for 2 cables and one entry for cable and tube

Equipment

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Safety

Protection index IP IP55

REACH conform Yes

RoHS conform Yes

Halogen free Yes

With enhanced contact protection Yes

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

Identification

Application, usage

Surface-mounted wet-room installation

Main design line

Berker W.1

Instructions

Information text

Hinged cover springs made of stainless steel, pins of
quick-release lock made of ZAMAK