



47803515

**Combi. change-over switch/SCHUKO soc.out. hinged cov surf.-mtd, W.1, grey m.**

**Technical characteristics**

**Configuration**

Hollow base ample room for wiring under the bases of the inserts

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 16 A

**Electric current**

Switching current 10 AX

**Cover, door**

Hinged covers with hinged cover that falls back, manual clip-in

**Installation, mounting**

Installation mode for vertical mounting

**Connection**

Type of connection with plug-in terminals

**Cable**

Wire with one entry for 2 cables and one entry for cable and tube

**Equipment**

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Switches / socket outlets change-over switch and socket outlet connectable separately

**Use conditions**

Operating temperature -40...30 °C

Storage/transport temperature -50...50 °C

**Identification**

Application, usage Surface-mounted wet-room installation

Main design line Berker W.1

**Instructions**

Information text Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK