



47903512

Combi.switch/SCHUKO soc.out. hinged cover surf.-mtd,enhncd contact prot.,W1

Technical characteristics

Configuration

Hollow base	ample room for wiring under the bases of the inserts
Number of modules	1

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	16 A

Electric current

Switching current	10 AX
-------------------	-------

Cover, door

Hinged covers	with hinged cover that falls back, manual clip-in
---------------	---

Installation, mounting

Installation mode	for vertical mounting
-------------------	-----------------------

Connection

Connection terminals	according to VDE 0620-1
Terminal	with Wago clip-in 2-wire connection terminal for wiring ; with two clip-in places for Wago 2-wire connection terminals in the housing floor
Type of connection	with plug-in terminals

Cable

Wire	with one entry for 2 cables and one entry for cable and tube
------	--

Equipment

Sealing	with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Switches / socket outlets	series switch and socket outlet connectable separately

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-15...30 °C
-----------------------	-------------

Identification

Application, usage

Surface-mounted wet-room installation

Main design line

Berker W.1

Instructions

Information text

Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK