



47903512

**Combi.switch/SCHUKO soc.out. hinged cover surf.-mtd,enhncd contact prot.,W1**

**Technical characteristics**

**Configuration**

Hollow base	ample room for wiring under the bases of the inserts
Number of modules	1

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	16 A

**Electric current**

Switching current	10 AX
-------------------	-------

**Cover, door**

Hinged covers	with hinged cover that falls back, manual clip-in
---------------	---

**Materials**

Material	thermoplastic
----------	---------------

**Installation, mounting**

Installation mode	for vertical mounting
-------------------	-----------------------

**Connection**

Connection terminals	according to VDE 0620-1
Terminal	with Wago clip-in 2-wire connection terminal for wiring, with two clip-in places for Wago 2-wire connection terminals in the housing floor
Type of connection	with plug-in terminals

**Cable**

Wire	with one entry for 2 cables and one entry for cable and tube
------	--

**Equipment**

Sealing	with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Switches / socket outlets	series switch and socket outlet connectable separately

**Safety**

Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

<b>Use conditions</b>	
Operating temperature	-15...30 °C
<b>Identification</b>	
Application, usage	Surface-mounted wet-room installation
Main design line	Berker W.1
<b>Instructions</b>	
Information text	Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK