



503203

## Push-button NC contact and NO contact with isolated input terminals

### Technical characteristics

#### Architecture

Type of control unit	rocker
----------------------	--------

#### Functions

Switching angle	3.5 °
-----------------	-------

#### Configuration

Switch mode	1 NO, 1 NC, separate input terminals
-------------	--------------------------------------

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

#### Electric current

Momentary-contact current	10 A
---------------------------	------

#### Dimensions

Depth	41.6 mm
Insertion depth	30.9 mm
Height	71 mm
Width	71 mm

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1
Lighting	for lighting and monitoring circuit

#### Use cases

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

#### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	Yes

#### Identification

Instructions

Information text

spreader claws, insulated to the supporting ring, self-  
resetting