



503203

## Push-button NC contact and NO contact with isolated input terminals

### Technical characteristics

#### Architecture

Type of control unit rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode 1 NO, 1 NC, separate input terminals

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 41.6 mm

Insertion depth 30.9 mm

Height 71 mm

Width 71 mm

#### Installation, mounting

Installation mode with spreader claws

#### Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

#### Use cases

Application Barrier-free application ; HVAC-control ; Light control

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

#### Identification

**Instructions**

---

Information text

spreader claws, insulated to the supporting ring, self-resetting