



503404

Group push-button, 4NO contacts, comm. input terminal, neut. pos., light control

Technical characteristics

Architecture

Type of control unit double rocker

Configuration

Switch mode with neutral position

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting for illumination

Use cases

Application Blind control, Light control

Use

Safety

Protection index IP

IP20

Identification

Application, usage

Light control

Main design line

Light control

Instructions

Information text

spreader claws, insulated to the supporting ring, self-resetting