



5036

## Push-button change-over contact illuminated

### Technical characteristics

#### Architecture

Type of control unit rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode change-over contact, usable as NC or NO

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

#### Materials

Material Plastic/metal

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Conductor cross-section (rigid) 2.5

Type of connection with plug-in terminals

#### Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

#### Use cases

Application Barrier-free application, HVAC-control, Light control

**Safety**

---

Protection index IP

IP20

**Identification**

---

Main design line

Light control

**Instructions**

---

Information text

spreader claws, insulated to the supporting ring, self-resetting