



5036

## Push-button change-over contact illuminated

### Technical characteristics

#### Architecture

Type of control unit rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode change-over contact, usable as NC or NO

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Conductor cross-section (rigid) max. 2.5 mm<sup>2</sup>

Type of connection with plug-in terminals

#### Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

#### Use cases

Application Barrier-free application ; HVAC-control ; Light control

#### Safety

REACH conform Yes

---

RoHS conform	Yes
Halogen free	Yes

---

**Identification**

---

Main design line	Light control
------------------	---------------

---

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--