



503601

**Push-button, NO contact, light control**

**Technical characteristics**

**Architecture**

Type of control unit rocker

**Functions**

Switching angle 3.5 °

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 10 A

**Dimensions**

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

**Connection**

Conductor cross-section (rigid) max. 2.5 mm<sup>2</sup>

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

**Use cases**

Application Light control

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Identification**

Application, usage Light control

Main design line Light control