



503601

Push-button, NO contact, light control

Technical characteristics

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

Connection

Conductor cross-section (rigid) max. 2.5 mm²

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Use cases

Application Light control

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Identification

Application, usage Light control

Main design line Light control