



503601

Push-button, NO contact, light control

Technical characteristics

Architecture

Type of control unit	rocker
----------------------	--------

Functions

Switching angle	3.5 °
-----------------	-------

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	250 V AC
---------------	----------

Electric current

Momentary-contact current	10 A
---------------------------	------

Dimensions

Depth	42 mm
-------	-------

Insertion depth	31 mm
-----------------	-------

Height	71 mm
--------	-------

Width	71 mm
-------	-------

Connection

Conductor cross-section (rigid)	max. 2.5 mm ²
---------------------------------	--------------------------

Connection terminals	according to IEC 60669-1
----------------------	--------------------------

Connection terminals	according to VDE 0632-1
----------------------	-------------------------

Type of connection	with plug-in terminals
--------------------	------------------------

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Light control
------------------	---------------