



50423515

**Push-button insert, 2 NO contacts rocker 2g surf./flushmtd comm. input ,W1, grey**

#### Technical characteristics

##### Main electrical features

Rated voltage	250 V AC
---------------	----------

##### Electric current

Momentary-contact current	10 A
---------------------------	------

##### Connection

Type of connection	with plug-in terminals
--------------------	------------------------

##### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

##### Use conditions

Operating temperature	-40...30 °C
-----------------------	-------------

Storage/transport temperature	-50...50 °C
-------------------------------	-------------

##### Identification

Application, usage	Surface-mounted wet-room installation
--------------------	---------------------------------------

Main design line	Berker W.1
------------------	------------

##### Instructions

Special note text	Inserts will only reach the degree of protection IP55 if mounted with a housing surface mounted or frame for flush-mounted installation.
-------------------	--

Information text	Pins of quick-release lock made of ZAMAK
------------------	--