



50453515

Push-button insert, NO contact rocker surface-mtd/flush-mtd, W.1, grey matt LT

Technical characteristics

Main electrical features

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Connection

Type of connection with plug-in terminals

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -40...30 °C

Storage/transport temperature -50...50 °C

Identification

Main design line Berker W.1

Instructions

Special note text Inserts will only reach the degree of protection IP55 if mounted with a housing surface mounted or frame for flush-mounted installation.

Information text Pins of quick-release lock made of ZAMAK