



510040

Surface-mtd push-button/pilot lamp E10, NO contact, surface-mtd, white glossy

Technical characteristics

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Momentary-contact current	2 A
---------------------------	-----

Dimensions

Depth	41.5 mm
Height	61.2 mm
Width	61 mm

Materials

Colour independent of design lines	white
Colour	white
Colour	white
Surface appearance	glossy

Incandescent bulbs control

Incandescent lamp power	max. 2 W
-------------------------	----------

Installation, mounting

Opening	knock out opening for entry at top and bottom
---------	---

Connection

Type of connection	with screw terminals
--------------------	----------------------

Cable

Wire	with line and duct entry
------	--------------------------

Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Identification

Application, usage	Dry surface-mounted installation
Main design line	Surface-mounted