



510040

**Surface-mtd push-button/pilot lamp E10, NO contact, surface-mtd, white glossy**

**Technical characteristics**

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC

**Electric current**

Momentary-contact current	2 A
---------------------------	-----

**Dimensions**

Depth	41.5 mm
Height	61.2 mm
Width	61 mm

**Materials**

Colour independent of design lines	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	duroplastic

**Incandescent bulbs control**

Incandescent lamp power	max. 2 W
-------------------------	----------

**Installation, mounting**

Opening	knock out opening for entry at top and bottom
---------	---

**Connection**

Type of connection	with screw terminals
--------------------	----------------------

**Cable**

Wire	with line and duct entry
------	--------------------------

**Equipment**

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

**Safety**

Protection index IP	IP20
---------------------	------

**Identification**

Application, usage	Dry surface-mounted installation
Main design line	Surface-mounted