



5101

## Push-button and pilot lamp E10 module inserts

### Technical characteristics

#### Configuration

Switch mode	Normally open contact
-------------	-----------------------

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

#### Electric current

Momentary-contact current	2 A
---------------------------	-----

#### Dimensions

Depth	30.4 mm
Insertion depth	29.3 mm
Height	71 mm
Width	71 mm

#### Materials

Material	Plastic/metal
----------	---------------

#### Incandescent bulbs control

Incandescent lamp power	max. 2 W
-------------------------	----------

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

#### Use cases

Application	Light control
-------------	---------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Identification

Application, usage	Light control
Main design line	Light control