



510110

## Push-button and pilot lamp E10 module inserts

### Technical characteristics

#### Configuration

Switch mode NO, with separate signalling contacts

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 2 A

#### Dimensions

Depth 30.1 mm

Insertion depth 28.8 mm

Height 70.8 mm

Width 70.8 mm

#### Incandescent bulbs control

Incandescent lamp power max. 2 W

#### Connection

Type of connection with screw terminals

#### Equipment

Lighting for lighting and monitoring circuit

#### Use cases

Application Light control

#### Identification

Application, usage Light control

Main design line Light control