



513040

Pilot lamp E14 surface-mtd, surface-mtd, white glossy

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Rated voltage 250 V AC

Materials

Colour independent of design lines white

Colour white

Colour white

RAL colour RAL 1013 - Oyster white

Material Plastic/metal

Lighting control

Long lamp base max. 23.5 mm

Incandescent bulbs control

Incandescent lamp power max. 3 W

Installation, mounting

Opening knock out opening for entry at top and bottom

Connection

Type of connection with screw terminals

Cable

Wire with line and duct entry

Identification

Application, usage Dry surface-mounted installation

Main design line Surface-mounted