



513040

Pilot lamp E14 surface-mtd, surface-mtd, white glossy

Technical characteristics

Main electrical features

Rated voltage 250 V AC

Materials

Colour independent of design lines white

Colour white

Colour white

Surface appearance glossy

Lighting control

Long lamp base max. 23.5 mm

Incandescent bulbs control

Incandescent lamp power max. 3 W

Installation, mounting

Opening knock out opening for entry at top and bottom

Connection

Type of connection with screw terminals

Cable

Wire with line and duct entry

Safety

Halogen free No

Identification

Application, usage Dry surface-mounted installation

Main design line Surface-mounted