



52036089

## Light signal frame, Q.1, p. white velvety

### Technical characteristics

#### Network configuration

Network	call tone received on voltage failure and return
---------	--

#### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	velvety

#### LED control

LED	with 4 red LEDs
-----	-----------------

#### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
Installation mode	centre plate for plug-in fixing

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Equipment

Buzzer/siren	call tone can be set as continuous signal or as pulses, acoustic call tone switchable on pilot lamp
Potential-free	with potential-free relay contact for call tone forwarding, e.g. to telephone dialler

#### Use cases

Application	Hospital application
-------------	----------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

#### Identification

Main design line	Berker Q.1
------------------	------------

#### Instructions

Information text	Recommendation: use deep box.
------------------	-------------------------------