



52046089

Mains adapter frame, Q.1, p. white velvety

Technical characteristics

Main electrical features

Frequency 50-60 Hz

Voltage

Input voltage 100...240 V AC

Output voltage 24 V DC

Electric current

Input current max. 180 mA

Output current max. 250 mA

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Installation mode centre plate for plug-in fixing

Connection

Type of connection with screw terminals

Use cases

Application Hospital application

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -5...40 °C

Identification

Main design line Berker Q.1

Instructions

Information text Recommendation: use deep box.