



6161036084

Socket outlet without earthing contact, Q.x, alu velvety, lacquered

Technical characteristics

Architecture

Number of poles 2pole

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Mirror depth 8 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

Metallic colour Yes

Installation, mounting

Installation mode for screw fastening

Connection

Connection terminals according to IEC 60884-1

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free	No
Protection	without enhanced contact protection
Identification	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9