



6167031909

Soc. out. out earthing contact, S.1/B.3/B.7, p. white, matt, plastic

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	32 mm
Mirror depth	8 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with plug-in terminals

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Protection

without enhanced contact protection

Identification

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7