



6167032045

Soc. out. out earthing contact, R.1/R.3, black glossy

Technical characteristics

Architecture

Number of poles 2pole

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Dimensions

Insertion depth 32 mm

Mirror depth 8 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 217,217,217

Colour of design line black

Material for printing PC-PMA black

Surface appearance glossy

Installation, mounting

Installation mode without spreader claws

Connection

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

Settings

Shading parameter R1_czarny

Laser parameter R1_schwarz

Equipment

Type of configuration Laserdruck

Safety

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8