



6167032089

## Soc. out. out earthing contact, R.1/R.3, p. white glossy

### Technical characteristics

#### Architecture

Number of poles 2pole

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

Mirror depth 8 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of labelling 105,105,105

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material for printing ASA polar white

Surface appearance glossy

#### Installation, mounting

Installation mode without spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

#### Settings

Shading parameter R1\_biały

Laser parameter R1\_weiß

#### Equipment

Type of configuration Laserdruck

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection

---

**Identification**

---

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

---