



6167036084

## Socket outlet without earthing contact, Q.x, alu velvety, lacquered

### Technical characteristics

#### Architecture

Number of poles 2pole

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Mirror depth 8 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

Metallic colour Yes

#### Installation, mounting

Installation mode without spreader claws ; for screw fastening

#### Connection

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

#### Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection without enhanced contact protection

**Identification**

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9