



6719333505

Surface-mounted lower casing 2gang vertical, w. frame and cable entries W.1 grey

Technical characteristics

Dimensions

Depth 56 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode for vertical mounting

Cable

Wire with one entry for 2 cables and one entry for cable and tube

Equipment

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -15...30 °C

Identification

Application, usage Surface-mounted wet-room installation

Main design line Berker W.1

Instructions

Special note text The degree of protection IP55 will only be reached if mounted with a modular flush-mounted insert of the Berker W.1 product line