



67303909

## Change-over switch, 2-pole 10 AX, light control

### Technical characteristics

#### Configuration

Switch mode	2-pole off/change-over
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

#### Electric current

Switching current	10 AX
-------------------	-------

#### Dimensions

Depth	42 mm
Insertion depth	31 mm
Height	71 mm
Width	71 mm

#### Materials

Surface appearance	other
--------------------	-------

#### Connection

Type of connection	with screw terminals
Type of connection	Screw connection

#### Equipment

Lighting	for illumination ; can be illuminated with neon lamp unit
Heating switch	No

#### Use cases

Application	Light control
-------------	---------------

#### Safety

Impact strength	IK05
-----------------	------

#### Identification

Application, usage	Light control
Main design line	Light control