



67303909

Change-over switch, 2-pole 10 AX, light control

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Configuration

Switch mode	2-pole off/change-over
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	10 AX
-------------------	-------

Dimensions

Depth	42 mm
Insertion depth	31 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
Surface appearance	other

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	for illumination, can be illuminated with neon lamp unit
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
Impact strength	IK05

Identification

Application, usage

Light control

Main design line

Light control