



6765092003

Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,R.1.3,green

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of labelling	217,217,217
Design lines special colours	green
Colour	green
Colour	green
RAL colour	RAL 6029 - Mint green
Material	thermoplastic
Material for printing	ABS green

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

Safety

Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8

Instructions

Information text	Insert colour-coded.
------------------	----------------------
