



6765092007

**Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,R.1.3,orange**

#### Technical characteristics

##### Architecture

Number of poles 2pole + earth

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of labelling 217,217,217

Design lines special colours orange

Material for printing ABS orange

Surface appearance glossy

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

##### Equipment

Type of configuration Laserdruck

##### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

##### Safety

Halogen free No

Protection Enhanced contact protection

**Identification**

---

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1 ; Berker R.3 ; Berker R.8

**Instructions**

---

Information text

Insert colour-coded.