



6765092022

**Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,R.1.3,red**

**Technical characteristics**

**Architecture**

Number of poles 2pole + earth

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of labelling 217,217,217

Design lines special colours red

Material for printing ABS red

Surface appearance glossy

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

**Equipment**

Type of configuration Laserdruck

**Use**

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

**Safety**

RoHS conform Yes

Halogen free No

Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
<b>Instructions</b>	
Information text	Insert colour-coded.