



6765092089

**Soc.out. earth.pin+control LED,enhncd contact prot.,screw-in lift term.,R.1.3,wh**

#### Technical characteristics

##### Architecture

Number of poles 2pole + earth

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of labelling 105,105,105

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material for printing ASA polar white

Surface appearance glossy

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

##### Settings

Shading parameter R1\_biały

Laser parameter R1\_weiß

##### Equipment

Type of configuration Laserdruck

##### Use

---

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

Differentiation characteristic 3 - Sales	Screw-in lift terminals
--	-------------------------

---

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Protection	Enhanced contact protection
------------	-----------------------------

With enhanced contact protection	Yes
----------------------------------	-----

---

**Identification**

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
--------------------------	--------------------------------------