



6765092089

**Soc.out. earth.pin+control LED,enhncd contact prot.,screw-in lift term.,R.1.3,wh**

**Technical characteristics**

**Architecture**

Fixing mode	flush-mounting
Number of poles	2pole + earth

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

**Settings**

Shading parameter	R1_biały
Laser parameter	R1_weiß

**Equipment**

Type of configuration	Laserdruck
-----------------------	------------

**Use**

---

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

---

Differentiation characteristic 3 - Sales	Screw-in lift terminals
--	-------------------------

**Safety**

---

Protection	Enhanced contact protection
------------	-----------------------------

---

With enhanced contact protection	Yes
----------------------------------	-----

**Identification**

---

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

---

Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
--------------------------	------------------------------------