



6765762045

**Soc.out. earth. pin, enhncd contact prot., screw-in lift term., R.1/R.3, bl. gl.**

#### Technical characteristics

##### Architecture

Number of poles 2pole + earth

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of labelling 217,217,217

Colour of design line black

Material for printing PC-PMA black

Surface appearance glossy

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

##### Settings

Shading parameter R1\_czarny

Laser parameter R1\_schwarz

##### Equipment

Type of configuration Laserdruck

##### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales with screw-in lift terminals

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

---

**Identification**

---

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

---