



6765792045

Soc.out. earth. pin, enhncd contact prot., screw-in lift term.,R.classic, bl.gl.

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	31.4 mm
-----------------	---------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Use	
Differentiation characteristic 1 - Sales	Installation position variable in 45° steps
Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw-in lift terminals
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
Identification	
Main design line	Serie R.classic