



6765832089

Soc.out. earth.pin+hinged cover,enhncd contact prot.,screw-in lift term.,R1.3,wh

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	31.3 mm
Mirror depth	14.5 mm

Cover, door

Hinged covers	with self-closing hinged covers
Cover	Central cover plate

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

Settings

Shading parameter	R1_biały
Laser parameter	R1_weiß

Equipment

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw-in lift terminals

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107600).
-------------------	--