



6768766012

Soc. out. earthing pin, enhncd contact prot., Q.x, red velvety

Technical characteristics

Architecture

| | |
|-----------------|----------------|
| Fixing mode | flush-mounting |
| Number of poles | 2pole + earth |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |

Dimensions

| | |
|---|---------|
| Insertion depth | 32 mm |
| Installation depth, flush-mounted boxes | 31 mm |
| Mirror depth | 14.5 mm |

Cover, door

| | |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

Materials

| | |
|------------------------------|---------------------|
| Design lines special colours | red |
| Colour | red |
| Colour | red |
| RAL colour | RAL 3003 - Ruby red |
| Material | duroplastic |
| Surface appearance | velvety |
| Metallic colour | No |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Type of connection | with plug-in terminals |

Use

| | |
|--|--------------------------------|
| Differentiation characteristic 2 - Sales | with enhanced touch protection |
|--|--------------------------------|

Safety

| | |
|---|--|
| IK protection code against mechanical impacts | 02 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | Enhanced contact protection |
| With enhanced contact protection | Yes |
| Identification | |
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |