



6768766013

Soc. out. earthing pin, enhncd contact prot., Q.x, green velvety

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm
Mirror depth	14.5 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Design lines special colours	green
Colour	green
Colour	green
RAL colour	RAL 6029 - Mint green
Material	duroplastic
Surface appearance	velvety
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

Safety

IK protection code against mechanical impacts	02
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
Identification	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9