



6768766014

**Soc. out. earthing pin, enhncd contact prot., Q.x, orange velvety**

**Technical characteristics**

**Architecture**

Number of poles 2pole + earth

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Mirror depth 14.5 mm

**Cover, door**

Cover Central cover plate

**Materials**

Design lines special colours orange

Surface appearance velvety

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales with enhanced touch protection

**Safety**

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9