



676879

**Soc. out. earthing pin, enhncd contact prot., 1930/glass, p. white glossy**

#### Technical characteristics

##### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	16 A

##### Dimensions

Insertion depth	31.4 mm
Installation depth, flush-mounted boxes	31 mm
Mirror depth	14.5 mm

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	duroplastic
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with plug-in terminals

##### Use

Differentiation characteristic 1 - Sales	Installation position variable in 45° steps
Differentiation characteristic 2 - Sales	with enhanced touch protection

##### Safety

IK protection code against mechanical impacts	02
Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Serie 1930/Glas
Secondary design line(s)	Serie 1930, Serie 1930 Porzellan Made by Rosenthal, Serie Glass, Series R.classic