



6768803512

**Soc.out. insert earth.pin+hinged cover surf./flushmtd,enhncd contact prot.,W1,wh**

#### Technical characteristics

##### Architecture

|                 |               |
|-----------------|---------------|
| Number of poles | 2pole + earth |
|-----------------|---------------|

##### Main electrical features

|               |          |
|---------------|----------|
| Rated voltage | 250 V AC |
|---------------|----------|

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Cover, door

|               |   |
|---------------|---|
| Hinged covers | with hinged cover that falls back, manual clip-in |
|---------------|---|

##### Connection

|                    |                        |
|--------------------|------------------------|
| Type of connection | with plug-in terminals |
|--------------------|------------------------|

##### Use

|  |                                |
|--|--------------------------------|
| Differentiation characteristic 2 - Sales | with enhanced touch protection |
|--|--------------------------------|

##### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

|                                  |     |
|----------------------------------|-----|
| With enhanced contact protection | Yes |
|----------------------------------|-----|

##### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -15...30 °C |
|-----------------------|-------------|

|                               |             |
|-------------------------------|-------------|
| Storage/transport temperature | -50...50 °C |
|-------------------------------|-------------|

##### Identification

|                  |            |
|------------------|------------|
| Main design line | Berker W.1 |
|------------------|------------|

##### Instructions

|                   |  |
|-------------------|--|
| Special note text | Inserts will only reach the degree of protection IP55 if mounted with a housing surface mounted or frame for flush-mounted installation. |
|-------------------|--|

|                  |  |
|------------------|--|
| Information text | Pins of quick-release lock made of ZAMAK |
|------------------|--|