



75040004

KNX data interface USB flush-mtd, KNX, black

Technical characteristics

Compatibility

Compatibility	compatible with USB 1.1/2.0 transmission protocols
System requirements:	system requirements: Windows 2000 or later

Connectivity

Connectors / jacks	with B-type USB socket for data traffic (voltage supply via PC)
--------------------	---

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Storage

Data transmission rate	max. 9.6 kBd
------------------------	--------------

Materials

Colour independent of design lines	black
Colour	black
Surface appearance	mat

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Cable

USB cable length	max. 5 m
------------------	----------

Settings

Supported configuration modes	system
Programming	programmable from ETS3, V1.0 ; For addressing, programming and diagnosis of KNX components

Equipment

Interface type	USB
Product type:	product type: USB

Software

Update	with flash-controller technology
--------	----------------------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature

-5...45 °C

Identification

Application, usage

KNX - system units

Product family

product family: communication

Main design line

KNX