



75040004



## KNX data interface USB flush-mtd, KNX, black

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Compatibility

Compatibility compatible with USB 1.1/2.0 transmission protocols

System requirements: system requirements: Windows 2000 or later

#### Connectivity

Connectors / jacks with B-type USB socket for data traffic (voltage supply via PC)

#### Voltage

Operating voltage over bus 21...32 V DC

#### Dimensions

Width of rail mounted device (RMD) 0 modules

#### Storage

Data transmission rate max. 9.6 kBd

#### Materials

Colour independent of design lines black

Colour black

RAL colour RAL 9005 - Jet black

Material Plastic/metal

Surface appearance matt

#### Installation, mounting

Installation mode without spreader claws

#### Cable

USB cable length max. 5 m

#### Settings

Supported configuration modes system

Programming programmable from ETS3, V1.0, For addressing, programming and diagnosis of KNX components

#### Equipment

Interface type USB

Product type: product type: USB

#### Software

Update

with flash-controller technology

---

**Safety**

Protection index IP

IP20

---

**Use conditions**

Operating temperature

-5...45 °C

---

**Identification**

Application, usage

KNX - system units

Product family

product family: communication

Main design line

KNX