



75161090

IP20

## B.IQ push-button 1gang, KNX - B.IQ, glass p. white

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

#### Compatibility

Extension unit extension unit for light scene push-button

#### Controls and indicators

With LED indication Yes

Number of buttons 1

#### Dimensions

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

#### Measurement

Value transmitter dimming / position value transmitter 1 byte

#### Screen

With display No

#### Materials

Colour of design line glass polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material glass

Surface appearance glossy

Type of surface treatment Painted

#### LED control

LED with blue operation LED and 2 white status LEDs (labelling field illumination)

#### Connection

Bus coupling unit for bus coupling unit flush-mounted

#### Scope of delivery

Bus connection included

No

### Accessories included

Box for installation in single standard wall boxes

Matching products

for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

### Equipment

Number of actuation points 2

With anti-theft/dismantling protection Yes

Product type: product type: B.IQ

### Safety

Protection index IP IP20

Protection with dismantling protection

### Use conditions

Operating temperature -5...45 °C

### Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker B.IQ

Secondary design line(s) Berker B.IQ ; KNX