



75161090



IP20

## B.IQ push-button 1gang, KNX - B.IQ, glass p. white

### Technical characteristics

#### Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Number of buttons	1

#### Dimensions

Assembling height	16.7 mm
Height	88.5 mm
Width	88.5 mm

#### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

#### Screen

With display	No
--------------	----

#### Materials

Colour of design line	glass polar white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

#### LED control

LED	with blue operation LED and 2 white status LEDs (labelling field illumination)
-----	--

#### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

#### Scope of delivery

Bus connection included	No
-------------------------	----

#### Accessories included

Box	for installation in single standard wall boxes
-----	--

for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

---

**Equipment**

Number of actuation points	2
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

---

**Safety**

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

---

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

---

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ ; KNX