



75161099



IP20

B.IQ push-button 1gang, KNX - B.IQ, p. white, matt, plastic

Technical characteristics

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	1

Dimensions

Assembling height	16.7 mm
Height	88.5 mm
Width	88.5 mm

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt
Type of surface treatment	untreated

LED control

LED	with blue operation LED and 2 white status LEDs (labelling field illumination)
-----	--

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
-----	--

for plastic frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

Equipment

Number of actuation points	2
With anti-theft/dismantling protection	Yes
Type of configuration	Laserdruck
Product type:	product type: B.IQ

Safety

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ ; KNX